


UL SYSTEM NO. F-C-2263

CLOSET FLANGE IN WOOD FLOOR/CEILING ASSEMBLY

F-RATING = 1-HR.

T-RATING = 1-HR.

CROSS-SECTIONAL VIEW



1. WOOD FLOOR/CEILING ASSEMBLY (UL CLASSIFIED L500 SERIES) (1-HR. FIRE-RATING).
2. DRAIN PIPING AND 90° ELBOW TO BE ONE OF THE FOLLOWING :
 - A. NOMINAL 4" DIAMETER PVC PLASTIC PIPE (SCHEDULE 40).
 - B. NOMINAL 4" DIAMETER ABS PLASTIC PIPE (SCHEDULE 40).
3. PVC OR ABS CLOSET FLANGE SIZED TO ACCOMMODATE DRAIN PIPE. CLOSET FLANGE SECURED TO PLYWOOD SUBFLOOR WITH STEEL SCREWS.
4. MINIMUM 3/4" DEPTH HILTI CP 606 FLEXIBLE FIRESTOP SEALANT OR HILTI FS-ONE MAX OR FS-ONE INTUMESCENT FIRESTOP SEALANT.
5. (NOT SHOWN). FLOOR MOUNTED VITREOUS WATER CLOSET.

NOTE : DIAMETER OF OPENING TO BE MAXIMUM 1/2" LARGER THAN OUTSIDE DIAMETER OF CLOSET FLANGE.



Hilti Firestop Systems

HILTI, Inc.
Tulsa, Oklahoma USA (800) 879-8000

Sheet	1 of 1
Scale	5/32" = 1"
Date	Jan. 07, 2015

Drawing No.

**FC
2263d**

Saving Lives through Innovation and Education

FC2263d.010715