

SELECT ANCHOR
✕

FILTER Clear all filters

Search for something ...

Default ▼

Calculate all ▶

Fixture thickness

Min Max

+
-

Hole diameter

Min Max

+
-

Anchor type ⓘ

Mechanical

Adhesive

Corrosion / material ⓘ

Galvanized steel

Sheradized, hot dip galvanized

Sheradized, hot dip galvanized, mechanically galvanized

Stainless steel

High corrosion resistant steel

Cleaning ⓘ

SafeSet - no cleaning required

SafeSet - automatic cleaning

Manual cleaning

Compressed air cleaning

Traceable anchors (Data Matrix Code)

with Data Matrix Code

Setting ⓘ

Pre-setting

Through-fastening

Thread type ⓘ

External thread













Internal thread

No thread

Head configuration ⓘ

Countersunk head

Dome nut

	<p>HUS4-H Bonded Screw MAX capsule mortar with HUS screw anchor</p>	☆	
	<p>HUS4-C Bonded Screw MAX capsule mortar with HUS screw anchor</p>	☆	
	<p>HIT-HY 200-R V3 + Rebar HIT-HY 200-R V3 injection mortar with Rebar</p>	☆	
	<p>HIT-HY 200-R V3 + Rebar 100 Years HIT-HY 200-R V3 injection mortar with Rebar</p>	☆	
	<p>HIT-RE 500 V4 + Rebar HIT-RE 500 V4 injection mortar with Rebar</p>	☆	
	<p>HIT-RE 500 V4 100 Years + Rebar HIT-RE 500 V4 injection mortar with Rebar</p>	☆	

ANCHOR ⓘ

Calculate all ▶

Adhesive

No thread

 HUS4-H Bonded Screw ☆

 HUS4-C Bonded Screw ☆

 HIT-HY 200-R V3 + Rebar ☆

 HIT-HY 200-R V3 + Rebar 100 Years ☆

 HIT-RE 500 V4 + Rebar ☆

 HIT-RE 500 V4 100 Years + Rebar ☆

Type

HIT-RE 500 V4 + Rebar ▼

Size

12mm ▼

View ETA approval

Embedment depth h_{ef}





⬇️ Design loads
⬇️ Sustained loads

S	C	Total

⬇️ Import load combinations