

Drill bit diameter	Drill hole depth at embed. 1	Drill hole depth at embed. 2	Max. fixture thickness at embed. 1	Max. fixture thickness at embed. 2	Base plate clearance hole
8 mm	-	60 mm	-	10 mm	9 mm
8 mm	-	60 mm	-	30 mm	9 mm
8 mm	-	60 mm	-	50 mm	9 mm
10 mm	53 mm		10 mm	-	9 mm
10 mm	53 mm	-	20 mm	-	9 mm
10 mm	53 mm	73 mm	30 mm	10 mm	12 mm
10 mm	53 mm	73 mm	50 mm	30 mm	12 mm