

HVU-TZ

Size	t _{fix, effective} (mm)
M8	t _{fix} - 8 mm
M10	t _{fix} - 9 mm
M12	t _{fix} - 10 mm
M16	t _{fix} - 11 mm
M20	t _{fix} - 13 mm

<p>CE</p> <p>15 HILTI AG, FL-9494 Schaan Hilti Werke 0672-CPR-0047 ETA-03/0032 Notified body 0672 ETAG 001-1, -5 Option 1 www.hilti.com</p>
--

HIT-Z(-R)

Size	t _{fix, effective} (mm)
M8	t _{fix} - 8 mm
M10	t _{fix} - 9 mm
M12	t _{fix} - 10 mm
M16	t _{fix} - 11 mm
M20	t _{fix} - 13 mm

<p>CE</p> <p>15 HILTI AG, FL-9494 Schaan Hilti Werke 1343-CPR-M 500-14/07.14 ETA-12/0006 Notified body 1343 ETAG 001-1, -5 Option 1, Seismic C1 (C2) www.hilti.com</p>	<p>CE</p> <p>15 HILTI AG, FL-9494 Schaan Hilti Werke 1343-CPR-M 500-15/07.14 ETA-12/0028 Notified body 1343 ETAG 001-1, -5 Option 1, Seismic C1 (C2) www.hilti.com</p>
---	---

HIT-V(-F) 8.8/AM (HDG) 8.8

Size	t _{fix, effective} (mm)
M16	t _{fix} - 11 mm
M20	t _{fix} - 13 mm
M24	t _{fix} - 15 mm

<p>CE</p> <p>16 HILTI AG, FL-9494 Schaan Hilti Werke 1343-CPR-M 500-23/07.14 ETA-16/0143 Notified body 1343 ETAG 001-1, -5 Option 1, Seismic C1 www.hilti.com</p>	<p>CE</p> <p>15 HILTI AG, FL-9494 Schaan Hilti Werke 1343-CPR-M 500-10/07.14 ETA-11/0493 Notified body 1343 ETAG 001-1, -5 Option 1 (Seismic C1) www.hilti.com</p>	<p>CE</p> <p>15 HILTI AG, FL-9494 Schaan Hilti Werke 1343-CPR-M 500-11/07.14 ETA-12/0084 Notified body 1343 ETAG 001-1, -5 Option 1 (Seismic C1) www.hilti.com</p>
--	---	---

HST3(-R)

Size	t _{fix, effective} (mm)
M8	t _{fix} - 8 mm
M10	t _{fix} - 9 mm
M12	t _{fix} - 10 mm
M16	t _{fix} - 11 mm
M20	t _{fix} - 13 mm

<p>CE</p> <p>17 HILTI AG, FL-9494 Schaan Hilti Werke 0432-CPR-00242-1 ETA-98/0001 Notified body 432 EAD 330232-00-060 Option 1, (Seismic C1, C2) www.hilti.group</p>

HDA-P(R)

1 t_{fix}
HDA-P(R)

1a

2

3 T_{inst}

4 T_{inst}
HDA-P(R)

5

6 $\frac{1}{4} - \frac{1}{2}$
 $t_{fix, effective}$

7 HIT-HY 200-A

8 T_{cure}
HIT-HY200 -A

9 T_{cure}
HIT-HY200 -A

Size	$t_{fix, effective}$ (mm)
M10	$t_{fix} - 6$ mm
M12	$t_{fix} - 7$ mm
M16	$t_{fix} - 8$ mm
M20	$t_{fix} - 4$ mm

HDA-T(R)

1 t_{fix}
HDA-T(R)

1a

2

3 T_{inst}

4 T_{inst}
HDA-T(R)

5

6 $\frac{1}{4} - \frac{1}{2}$
 $t_{fix, effective}$

7 HIT-HY 200-A

8 T_{cure}
HIT-HY200 -A

9 T_{cure}
HIT-HY200 -A

Size	$t_{fix, effective}$ (mm)
M10	$t_{fix} - 2$ mm
M12	$t_{fix} - 3$ mm
M16	$t_{fix} - 4$ mm
M20	$t_{fix} - 4$ mm

HUS3-H

1 t_{fix}
HUS3-H

2

3

4 T_{inst}
 $t_{fix, effective}$

5 HIT-HY 200-A

6 T_{cure}
HIT-HY200 -A

7 T_{cure}
HIT-HY200 -A

Size	Seismic Set	HUS3	$t_{fix, effective}$ (mm)
M10		8	$t_{fix} - 7$ mm
M12		10	$t_{fix} - 8$ mm
M16		14	$t_{fix} - 9$ mm

CE
0672
HILTI AG, FL-9494 Schaan
Hilti Werke
14
0672-CPR-0361
ETA-131039
ETAG 001-3 Option 1
Seismic C1
EAD 330011-00-0601

HMU-PF

1 t_{fix}
HMU-PF

1a

2

3 T_{inst}

4 T_{inst}
HMU-PF

5

6 $\frac{1}{4} - \frac{1}{2}$
 $t_{fix, effective}$

7 HIT-HY 200-A

8 T_{cure}
HIT-HY200 -A

9 T_{cure}
HIT-HY200 -A

Size	$t_{fix, effective}$ (mm)
M12	$t_{fix} - 10$ mm
M16	$t_{fix} - 11$ mm