

SELECT ANCHOR



FILTER

Clear all filters

Search for something ...

Default

Calculate all

Fixture thickness

Min  Max

Hole diameter

Min  Max

Anchor type

- Mechanical
- Adhesive

Corrosion / material

- Galvanized steel
- Sheradized, hot dip galvanized
- Sheradised, hot dip galvanized, mechanically galvanized
- Stainless steel
- High corrosion resistant steel

Cleaning

- SafeSet - no cleaning required
- SafeSet - automatic cleaning
- Manual cleaning
- Compressed air cleaning

Traceable anchors (Data Matrix Code)

- with Data Matrix Code








Setting

- Pre-setting
- Through-fastening

Thread type

- External thread
- Internal thread
- No thread

Head configuration

	<p><b>HIT-HY 200-R V3 100 Years + Rebar</b></p> <p>HIT-HY 200-R V3 injection mortar with Rebar</p>	☆	
	<p><b>HIT-HY 200-R V3 + Rebar 100 Years</b></p> <p>HIT-HY 200-R V3 injection mortar with Rebar</p>	☆	
	<p><b>HIT-RE 500 V4 + Rebar</b></p> <p>HIT-RE 500 V4 injection mortar with Rebar</p>	☆	
	<p><b>HIT-RE 500 V4 100 Years + Rebar</b></p> <p>HIT-RE 500 V4 injection mortar with Rebar</p>	☆	