



Company:		Page:	1
Address:		Specifier:	
Phone Fax:		E-Mail:	
Design:	Rebar - Mar 25, 2024	Date:	25. 03. 2024
Rebar application:			

Specifier's comments:

1. Input data

General

Design standard	ACI 318
Calculation method	Modified from ACI 318-19
Research-based design methods	Allowed
Post installed rebar approach	Joints + Anchoring for yield
Loading type	Static
Yield design	yes



Product

Mortar	HIT-HY 200 V3
Connector	Rebar #5
Item number	2334276 HIT-HY 200-R V3 (adhesive)
Effective embedment depth	Existing concrete: $h_{ef,ex} = 3.500$ in.
Material	ASTM A615 Grade 60
Evaluation Service Report	ESR-4868
Issued	01. 11. 2022
Valid	01. 11. 2024
Proof	Design method Modified from ACI 318-19
Epoxy coated reinforcement	no

Material


Concrete material	Cracked concrete, 4000, $f_c' = 4,000$ psi;
Surface contact condition	Option (c)
Reinforcement	tension: not present
Steel strain limit	0.02

Installation and temperature

Temperature	During service: 32 °F / 32 °F (short / long term)
Installation	Hammer Drilling, Installation Condition: Dry Concrete


1.1. Geometry & Loading

Geometrical dimensions in [in]. Loading values in [lb, in-lb]







1.2. Cross section view





1.3. Side section view





Company:		Page:	5
Address:		Specifier:	
Phone Fax:		E-Mail:	
Design:	Rebar - Mar 25, 2024	Date:	25. 03. 2024
Rebar application:			

2. Loads and Cross section analysis

2.1. Load combinations

Case	Description	Forces [lb] / Moments [in-lb]	Load type	Max. Utilization [%]	Embedment depth [in]
1	Combination 1	$N = 12,000; V_x = 0; V_y = 0;$ $M_x = 0; M_{x,sus} = 0; N_{sus} = 0;$	Static	-	3.500

Company:		Page:	6
Address:		Specifier:	
Phone Fax:		E-Mail:	
Design:	Rebar - Mar 25, 2024	Date:	25. 03. 2024
Rebar application:			

2.2. Cross section analysis ([1] Section 20.2, 21.2, 22.2, 22.3, 22.4)

User input

Rebar arrangement and diameter at the interface; see figure below

Description	Variable	Value
Reinforcement yield strength, post installed	$f_{y,PI}$	60,000 psi
Concrete compressive strength	f'_c	4,000 psi

Verification results at Ultimate Limit State

Input and assumptions

The cross section verification is performed on the assumption that plane sections remain plane. The (assumed) relationship between concrete compressive stress and strain is represented by a parabola-rectangle diagram. The following stress-strain relationship (Figure 3.3) for the design of the concrete cross-section under compression is used according to EN 1992-1-1, Section 3.1.7 (1).




Figure 3.3: Parabola-rectangle diagram for concrete under compression.

$$\sigma_c = f_{cd} \left[1 - \left(1 - \frac{\varepsilon_c}{\varepsilon_{c2}} \right)^n \right] \text{ for } 0 \leq \varepsilon_c \leq \varepsilon_{c2} \quad (3.17)$$

$$\sigma_c = f_{cd} \text{ for } \varepsilon_{c2} \leq \varepsilon_c \leq \varepsilon_{cu2} \quad (3.18)$$

where:

n is the exponent (=2)

ε_{c2} is the strain at reaching the maximum strength

Company:		Page:	7
Address:		Specifier:	
Phone Fax:		E-Mail:	
Design:	Rebar - Mar 25, 2024	Date:	25. 03. 2024
Rebar application:			

ϵ_{cu2} is the ultimate strain

The (bi-linear) design properties of the reinforcement (acc. to [1] section 20.2.2.1) are as follows. The stress below f_y shall be E_s times steel strain. For strains greater than that corresponding to f_y , stress shall be considered independent of strain and equal to f_y .


ϕ values acc. to [1] Table 21.2.1 (a) and 21.2.2:
 Net tensile strain acc. to [1] Table 21.2.2:

$$\phi_{T.C.} = 0.90, \phi_{C.C.} = 0.65$$

$$T.C.: \epsilon_t \geq \epsilon_{ty} + 0.003,$$

$$C.C.: \epsilon_t \leq \epsilon_{ty}$$

Interface results at Ultimate Limit State [in]



The compression zone / compressed rebar is / are the default area / rebar used for shear transfer.

Origin of the coordinate system (0, 0) is located at the geometrical center of the cross-section.

Verification

Variables

d_b [in]	f_{cd} [psi]	ϵ_{c2} [-]	ϵ_{cu2} [-]	$f_{y,PI}$ [psi]	ϵ_{ty} [-]	f'_c [psi]
0.625	3,400.001	0.0020	0.0030	60,000	0.0021	4,000

Calculations

ϵ_t [-]	c [in]	Tension ULS [lb]	Compression ULS [lb]
0.0021	0.000	73,631	-



Company:		Page:	8
Address:		Specifier:	
Phone Fax:		E-Mail:	
Design:	Rebar - Mar 25, 2024	Date:	25. 03. 2024
Rebar application:			

Results

ϕ [-]	ϕN_n [lb]	$\phi M_{x,n}$ [in-lb]
0.900	66,268	-0

3. Overview of results

3.1. References

[1] Building Code Requirements for Structural Concrete (ACI 318-19), Commentary on Building Code Requirements for Structural Concrete (ACI318R-19)

3.2. Anchoring to concrete ([1] Section 17)

User input

Description	Variable	Value
Rebar diameter	d_a	0.625 in
User-defined steel over-strength factor	Ω_{fy}	1.000
Reinforcement yield strength, post installed	$\Omega_{fy} \cdot f_{y,PI}$	60,000 psi
Concrete compressive strength	f'_c	4,000 psi

Embedment for yield and strength capacities in tension

Determined embedment $h_{ef} = 3.500$ in

Overview Table

Failure Mode	Capacity ϕN_n [lb] per rebar	Status
Steel strength	18,600	Ok
Bond strength	2,817	Not Ok
Concrete breakout strength	3,315	Not Ok

Steel strength

$$N_{sa} = A_{se,N} \cdot f_{y,PI}$$
$$\phi N_{sa}$$

[1] Table 17.5.2

Variables

$A_{se,N}$ [in ²]	$f_{y,PI}$ [psi]
0.31	60,000



<https://www.hilti.com/>

Company:		Page:	9
Address:		Specifier:	
Phone Fax:		E-Mail:	
Design:	Rebar - Mar 25, 2024	Date:	25. 03. 2024
Rebar application:			

Calculations

N_{sa} [lb]

18,600

Results

N_{sa} [lb]

18,600

Ω_{fy}

1.000

$\Omega_{fy} N_{sa}$ [lb]

18,600

Bond Strength

N_{ag}	$= \frac{A_{Na}}{A_{Na0}} \cdot \psi_{ec1,Na} \cdot \psi_{ec2,Na} \cdot \psi_{ed,Na} \cdot \psi_{cp,Na} \cdot N_{ba}$	[1] Eq. (17.6.5.1b)
ϕN_{ag}		[1] Table 17.5.2
A_{Na}	see [1] Section 17.6.5.1, Fig. R 17.6.5.1(b)	
A_{Na0}	$= (2c_{Na})^2$	[1] Eq. (17.6.5.1.2a)
c_{Na}	$= 10d_a \sqrt{\frac{\tau_{k,c,uncr}}{1100}}$	[1] Eq. (17.6.5.1.2b)
$\psi_{ec,Na}$	$= \left(\frac{1}{1 + \frac{e'_{N}}{c_{Na}}} \right) \leq 1.0$	[1] Eq. (17.6.5.3.1)
$\psi_{ed,Na}$	$= 0.7 + 0.3 \left(\frac{c_{a,min}}{c_{Na}} \right) \leq 1.0$	[1] Eq. (17.6.5.4.1b)
$\psi_{cp,Na}$	$= 1.0$	[1] Eq. (17.6.5.5.1b)
N_{ba}	$= \lambda_a \cdot \tau_{k,c} \cdot \pi \cdot d_a \cdot h_{ef}$	[1] Eq. (17.6.5.2.1)

Variables

$\tau_{k,c,uncr}$ [psi]	d_a [in]	h_{ef} [in]	$c_{a,min}$ [in]	$\tau_{k,c}$ [psi]
1,636	0.625	3.500	41.313	1,142
$e_{c1,N}$ [in]	$e_{c2,N}$ [in]	c_{ac} [in]	λ_a	
0.000	0.000	7.263	1.000	

Calculations

c_{Na} [in]	A_{Na} [in ²]	A_{Na0} [in ²]	$\psi_{ed,Na}$
7.587	508.44	230.24	1.000
$\psi_{ec1,Na}$	$\psi_{ec2,Na}$	$\psi_{cp,Na}$	N_{ba} [lb]
1.000	1.000	1.000	7,851



Company:		Page:	10
Address:		Specifier:	
Phone Fax:		E-Mail:	
Design:	Rebar - Mar 25, 2024	Date:	25. 03. 2024
Rebar application:			

Results

N_{ag} [lb]	ϕ_{bond}	ϕN_{ag} [lb]	$\frac{\phi N_{ag}}{n}$ [lb]
17,338	0.650	11,270	2,817

Concrete breakout strength

N_{cbg}	$= \left(\frac{A_{Nc}}{A_{Nc0}} \right) \cdot \psi_{ec,N} \cdot \psi_{ed,N} \cdot \psi_{c,N} \cdot \psi_{cp,N} \cdot N_b$	[1] Eq. (17.6.2.1b)
ϕN_{cbg}		[1] Table 17.5.2
A_{Nc}	see ACI 318-19, Section 17.6.2.1, Fig. R 17.6.2.1(b)	
A_{Nc0}	$= 9 \cdot h_{ef}^2$	[1] Eq. (17.6.2.1.4)
$\psi_{ec,N}$	$= \left(\frac{1}{1 + \frac{2e'_N}{3h_{ef}}} \right) \leq 1.0$	[1] Eq. (17.6.2.3.1)
$\psi_{ed,N}$	$= 0.7 + 0.3 \left(\frac{c_{a,min}}{1.5 \cdot h_{ef}} \right) \leq 1.0$	[1] Eq. (17.6.2.4.1b)
$\psi_{cp,N}$	$= 1.0$	[1] Eq. (17.6.2.6.1b)
N_b	$= k_c \cdot \lambda_a \cdot \sqrt{f'_c} \cdot h_{ef}^{1.5}$	[1] Eq. (17.6.2.2.1)

Variables

h_{ef} [in]	$e_{c1,N}$ [in]	$e_{c2,N}$ [in]	$c_{a,min}$ [in]	$\psi_{c,N}$
3.500	0.000	0.000	41.313	1.000
c_{ac} [in]	k_c	λ_a	f'_c [psi]	
7.263	17.000	1.000	4,000	

Calculations

A_{Nc} [in ²]	A_{Nc0} [in ²]	$\psi_{ec1,N}$	$\psi_{ec2,N}$	$\psi_{ed,N}$	$\psi_{cp,N}$	N_b [lb]
319.52	110.25	1.000	1.000	1.000	1.000	7,040

Results

N_{cbg} [lb]	$\phi_{concrete}$	ϕN_{cbg} [lb]	$\frac{\phi N_{cbg}}{n}$ [lb]
20,403	0.650	13,262	3,315



Company:		Page:	11
Address:		Specifier:	
Phone Fax:		E-Mail:	
Design:	Rebar - Mar 25, 2024	Date:	25. 03. 2024
Rebar application:			

4. Warnings

This design exclusively considers the local load transfer in the considered interface between new and existing concrete. The joint surfaces for concreting must be roughened to fulfil the design assumption.

The capacity of the cross-section has to be designed separately.

The installation (drilling, cleaning, setting) must be according to the approval!

The accessory list in this report is for the information of the user only. In any case, the instructions for use provided with the product have to be followed to ensure a proper installation.

The software does not check the minimum cover requirements to meet exposure conditions and exposure classes. It is the responsibility of the user to review minimum code requirements for concrete cover.

Yielding is not possible with your current configuration. Some factors that effect the calculations include spacing, edge distance, bar diameter, bar grade, and concrete strength. The Hilti Method may provide a solution with this configuration.

Anchor Design calculation results are shown for the average resistance per anchor

Using the Anchoring to Concrete Provisions to Design for Bar Yield does not result in an embedment depth less than development length. Some factors that affect these calculations include spacing, edge distance, bar diameter, bar grade, concrete strength, and strength reduction factor for concrete breakout and bond.

The results presented in this report have been calculated using a research-based design method. This design option provides an alternative to Code-based design methods, offering a more comprehensive solution for achieving optimal design results.

Interface does not meet the design criteria!



Company:		Page:	12
Address:		Specifier:	
Phone Fax:		E-Mail:	
Design:	Rebar - Mar 25, 2024	Date:	25. 03. 2024
Rebar application:			

5. Installation data

Mortar: HIT-HY 200 V3 + Rebar

Item number: 2334276 HIT-HY 200-R V3 (adhesive)

Connector: Rebar #5

Connector material: ASTM A615 Grade 60

Drilling method: Hammer Drilling

Hole type: Dry Concrete

Contact surface condition: Option (c)

Drill hole diameter in the base material: 0.750 in

Drill hole depth in the base material: 3.500 in

Minimum thickness of existing concrete: 3.500 in

Specification text: HIT-HY 200 V3 + Rebar #5 ASTM A615 Grade 60 with 3.500 in embedment depth

Top layer 1

Number of bars: 2

Top cover: 2.000 in

Side cover: 2.000 in

Bottom layer 1

Number of bars: 2

Bottom cover: 2.000 in

Side cover: 2.000 in



Company:		Page:	13
Address:		Specifier:	
Phone Fax:		E-Mail:	
Design:	Rebar - Mar 25, 2024	Date:	25. 03. 2024
Rebar application:			

6. Remarks; Your cooperation duties

Any and all information and data contained in the Software concern solely the use of Hilti products and are based on the principles, formulas and security regulations in accordance with Hilti's technical directions and operating, mounting and assembly instructions, etc., that must be strictly complied with by the user. All figures contained therein are average figures, and therefore use-specific tests are to be conducted prior to using the relevant Hilti product. The results of the calculations carried out by means of the Software are based essentially on the data you put in. Therefore, you bear the sole responsibility for the absence of errors, the completeness and the relevance of the data to be put in by you. Moreover, you bear sole responsibility for having the results of the calculation checked and cleared by an expert, particularly with regard to compliance with applicable norms and permits, prior to using them for your specific facility. The Software serves only as an aid to interpret norms and permits without any guarantee as to the absence of errors, the correctness and the relevance of the results or suitability for a specific application.

You must take all necessary and reasonable steps to prevent or limit damage caused by the Software. In particular, you must arrange for the regular backup of programs and data and, if applicable, carry out the updates of the Software offered by Hilti on a regular basis. If you do not use the AutoUpdate function of the Software, you must ensure that you are using the current and thus up-to-date version of the Software in each case by carrying out manual updates via the Hilti Website. Hilti will not be liable for consequences, such as the recovery of lost or damaged data or programs, arising from a culpable breach of duty by you.