

Flexible Firestop Sealant (CP 606)



Product description

- An acrylic based firestop sealant that provides movement capability in fire rated joints and seals through-penetrations applications

Areas of application

- Sealing construction/expansion joints
- Top-of-wall joints
- Metal pipes
- Cable bundles
- HVAC penetrations

For use with

- Various base materials such as masonry, concrete, gypsum, etc.
- Wall and floor assemblies rated up to 3 hours

Examples

- Where a gypsum wall assembly meets the underside of a metal or concrete deck
- Sealing expansion joints to impede the passage of fire, smoke and toxic fumes
- Sealing around HVAC penetrations through fire-rated assemblies



Product features

- Silicone free
- Halogen, asbestos and solvent free
- Paintable
- Tested up to 33% movement with 500 cycles in accordance to UL 2079 and ASTM 1966
- Smoke and fume resistant
- Easy clean up with water
- Single component systems available
- Meets LEED™ requirements for indoor environmental quality credit 4.1 Low Emitting Materials, Sealants and Adhesives and 4.2 Paints and Coatings

Technical Data*	CP 606
Chemical basis	Acrylic based firestop sealant
Color	Available in red, white and gray
Application temperature	40°F to 104°F (5°C to 40°C)
Skin-forming time	Approx. 15 min
Curing time	Approx. 3 mm / 3 days
Average volume shrinkage (ASTM C1241)	22.2%
Movement capability	Approx. 10%
Temperature resistance	-22°F to 176°F (-30°C to 80°C)
Surface burning characteristics (ASTM E 84-96)	Flame Spread: 10 Smoke Development: 0
Sound transmission classification (ASTM E 90-99)	56 (Relates to specific construction)
Shelf life¹⁾	24 Months
LEED VOC	75 g/l
Base materials	Concrete, Masonry, Drywall, Steel

Tested in accordance with

- UL 2079
- ASTM E 814
- ASTM E 1966
- ASTM E 84
- UL 1479
- ASTM G21

*At 73°F (23°C) and 50% relative humidity

Internationally Tested and approved



EN 1366-3

EN 1366-4



Ordering designation	Content per can/cartridge	Volume per unit	Sales pack quantity	Item number
CP 606 310ml white	310 ml	310 ml	1 pc	209625
CP 606 310ml INT grey	310 ml	310 ml	1 pc	209630
CP 606 580ml white	580 ml	580 ml	1 pc	209632
CP 606 5GAL white	19000 ml	19000 ml	1 pc	209637

Related Products



Dispensers

page no 56



CP 670

page no 28



Collars CP 643, CP 644

page no 44-46



Wraps CP 648-S, CP 648-E

page no 40-42

Installation instructions for CP 606

Notice

- Before handling, read Material Safety Data Sheet and product label for safe usage and health information.
- Instructions below are general guidelines — always refer to the applicable drawing in the UL Fire for complete installation information
- The use of backing material is recommended to control the sealant depth and help ensure assembly seal is complete

Opening

1. Clean the opening. Surfaces to which CP 606 will be applied should be cleaned of loose debris, dirt, oil, wax and grease. The surface should be moisture and frost free.

Application of firestop

2. Insert fill of mineral wool or backer rod (as required).
3. Apply firestop over backer rod.


4. Smooth firestop sealant with a trowel before the skin forms. Once cured, CP 606 can only be removed mechanically.
5. For maintenance reasons, a penetration seal can be permanently marked with an identification plate and fastened in a visible position next to the seal.

Not for use


- On areas immersed in water

Storage


- Store only in the original packaging in a location protected from moisture at a temperature of 40°F to 77°F (5°C to 25°C)
- Observe expiration date on package




1. Clean opening




2. Insert backing material compressed per UL System




3. Apply CP 606




4. Smooth CP 606




5. Fasten identification plate (if required)




1. Clean opening



2. Insert backing material



3. Apply CP 606



4. Smooth CP 606



5. Fasten identification plate (if required)