




PRIME TECH 7-555
GRAY RUST-INHIBITIVE PRIMER

**TECHNICAL
 DATA**

INDEX B
PAGE 1 OF 1



PRODUCT DESCRIPTION

To recoat: 20-30 minutes

Prime-Tech is a fast drying high solids modified alkyd corrosion inhibitive primer which is formulated for superior adhesion and wetting properties. It provides adhesion and corrosion resistance. This product withstands moderate weathering until finish coats are applied. Topcoats include, alkyds, and water borne finish coats

Shelf Life: one year
 Storage Temperature: 110°F Maximum
 Thinning: Ready to use. If thinning is required use acetone
 Equipment Cleanup: Clean equipment immediately after use with Xylene or lacquer thinner

BASIC USES:

Recommended uses: Excellent primer for properly prepared ferrous metals and steel. Structural steel, industrial equipment, ornamental iron, tanks, machinery, metal doors, frames and many more surfaces

LIMITATIONS:

- ◆ Substrate temperature must be above 45°F and below 85°F
- ◆ Do not apply in direct sunlight when temperature is above 80°F
- ◆ Do not apply in high humid or wet conditions
- ◆ Substrate must be cured and completely dry
- ◆ Do not use where hydrostatic pressure is possible
- ◆ Do not use on glazed ceramic tile, quarry tile, marble, terrazzo, dense brick, dense slate
- ◆ Do not apply on other sealers or coatings

PACKAGING:

1 Gallon Cans - 5 Gallon Pails - 55 Gallon Drums

PRECAUTIONS:

WARNING: FLAMMABLE. Keep away from heat, sparks, and flames. Do not smoke. Vapors may ignite explosively. Use in well-ventilated area. Avoid breathing vapors. Wear protective clothing, gloves and safety glasses. Harmful or fatal if swallowed. **KEEP OUT OF THE REACH OF CHILDREN.**

ANTIDOTES:

INGESTION: Do not induce vomiting. Call a physician.
EYES: Flush with large amounts of water for 15 minutes, holding eyelids open. If irritation persists see a physician.
INHALATION: Remove to fresh air and rest.
SKIN: Wash thoroughly with mild soap and water.

TECHNICAL DATA

VOC	Under 250 G/L
Sheen	Flat
Solids by wt	%70
Solids by volume	%49
Coverage	350-450 sq. ft/ gal
Flash Point	Flammable material, -4° F
DFT required	1.5- 2 mils
Drying Time:	At 77°F (25° C) and 55% relative humidity
	To touch: 20 minutes
	To Handle: 40 minutes

WARRANTY

The following warranty is made in lieu of all other warranties, either expressed or implied. This product is manufactured of selected raw materials by skilled technicians. Neither seller nor manufacturer has any knowledge or control concerning the purchaser's use. The only obligation of either seller or manufacturer shall be to replace any quantity of this product, which is proved to be defective. Any claim of defective product must be received in writing within one year from date of shipment. Neither seller nor manufacturer assumes any liability for injury, loss, or damage resulting from use of this product.