



49	STEEL Z-SHAPED CLIPS FORMED FROM STRIPS OF MINIMUM 20GA STEEL SIMILAR TO UL DESIGN NO. HW-D-0252. CLIPS TO EXTEND THROUGH THE THICKNESS OF THE SPRAY-APPLIED FIRE-RESISTIVE MATERIAL WITH 2" LONG UPPER AND LOWER LEGS. LEGS OF CLIPS TO FASTEN TO U/S FLOOR AND T/O STEEL STUDS. CLIPS SPACED MAX. 16" APART. MINIMUM 2 FASTENERS PER LEG.
50	ALL STUD OPENINGS TO BE DESIGNED, STAMPED & SEALED BY STUD CONTRACTORS STRUCTURAL ENGINEER
51	DEFLECTION TRACK
52	SPRAY-APPLIED FIRE SEALANT PER ULDESIGN NO. HW-D-0252 COLOUR: WHITE
53	50% COMPRESSED MINERAL WOOL FORMING MATERIAL PER UL DESIGN
54	FIRE RATED SEPARATION PER ULC DESIGN NO. W453 OR W411
55	MIN. 1/2" FIRE BARRIER SILICONE SEALANT EACH SIDE OF WALL BETWEEN FLUTTES OF THE STEEL FLOOR UNITS AND TOP OF WALL
56	PACKING MATERIAL FILL VOID WITH MINERAL WOOL BATT INSULATION MIN. 25% COMPRESSION