

# MATERIAL SAFETY DATA SHEET

**MANUFACTURER'S NAME:**

*STILES PAINT MFG, INC.  
21595 CURTIS ST  
HAYWARD, CA. 94545*

**EMERGENCY TELEPHONE:**

(510) 919-8167

**DATE OF PREPARATION:** 10/24/2013

**INFORMATION TELEPHONE NO:**

(510) 887-8868

---

## SECTION I - PRODUCT IDENTIFICATION

---

**PRODUCT NUMBER:** 7- 555  
**PRODUCT NAME:** 7- 555 GRAY PRIMER <250 G/L  
**PRODUCT CLASS:** ALKYD MODIFIED

---

## SECTION II - HAZARDOUS INGREDIENTS

---

INGREDIENT	CASE NUMBER	WEIGHT PERCENT	OCCUPATIONAL EXPOSURE LIMITS	VAPOR PRESSURE mm Hg @ TEMP
Alkyd Resin Solution	64741-65-7	10	300mg/m3 TWA/ACGIH	2.6 20C
Phenolic Alkyd Modified	Mixture	15	TWA: 50ppm, PEL: 100ppm	15.0 20C
2-Butoxyethanol*	111-76-2	<5	50ppm: PEL: 25ppm: TLV	.6 20C
Acetone*	67-64-1	<16	PEL-1000ppm, TLV-750ppm	180.0 20C

---

## SECTION III - PHYSICAL DATA

---

**BOILING RANGE:** 220 - 340 ° F

**VAPOR DENSITY:** Lighter Than Air

**EVAPORATION RATE:** Slower Than Ether

**% VOLATILE VOLUME:** 51.05 WT/GAL:11.75

VOC DOES NOT EXCEED 250 G/L

\* This chemical is a hazardous substance as defined by CERCLA 40 CFR part 302-4



---

## SECTION VII - SPILL OR LEAK PROCEDURES

---

### **STEPS TO BE TAKEN IN CASE MATERIAL IS RELEASED OR SPILLED:**

Eliminate ignition sources, provide good ventilation, dike spill area and add absorbent earth or sawdust to spilled liquid. Thoroughly wet with water and mix.

### **WASTE DISPOSAL METHOD:**

Collect absorbent/water/spilled liquid mixture into metal containers and add enough water to cover. Consult local, state, & federal hazardous waste regulation before disposing into approved hazardous waste landfills. Obey relevant laws.

---

## SECTION VIII - SAFE HANDLING AND USE INFORMATION

---

### **RESPIRATORY PROTECTION:**

When spraying this material use a NIOSH approved cartridge respirator or gas masked suitable to keep airborne mists vapor concentrations below the time weighted threshold limit values. When using in poorly ventilated and confined spaces, use a fresh-air supplying respirator or a self contained breathing apparatus.

### **VENTILATION:**

General mechanical ventilation or local exhaust should be suitable to keep vapor concentrations below TLV. Ventilation equip. must be explosion proof.

### **PROTECTIVE GLOVES:**

Impermeable chemical gloves for skin protection.

### **EYE PROTECTION:**

Use chemical safety glasses, goggles and face shield for eye protection.

### **OTHER PROTECTIVE EQUIPMENT:**

Use impermeable aprons and protective clothing whenever possible to prevent skin contact.

### **HYGIENIC PRACTICES:**

Eye washes and safety showers in the work place are recommended.

---

## SECTION IX - SPECIAL PRECAUTIONS

---

### **PRECAUTIONS TO BE TAKEN IN HANDLING AND STORING:**

Use non sparking utensils when handling this material. Avoid not metal surfaces, use in cool well ventilated areas. Keep containers closed when not in use. Keep away from excessive heat and open flames.

### **OTHER PRECAUTIONS:**

Smoking in areas where this material is used should be strictly prohibited.